


Data sheet | Item number: 211-821

Marker card; for Smart Printer; for use in nozzles; Length: 23 mm; white

www.wago.com/211-821



Data

Technical Data

Marking	plain
Marking	plain
Units per delivery form	2,500 markers/reel
Marking device	Smart Printer (Thermal Transfer Printer)

Geometrical Data

Depth	0,26 mm
Marking surface	4 x 23 mm

Mechanical data

Mounting type	Sliding
Smear resistance	smudge-proof in conjunction with 258-5005 Ink Ribbon

Subject to changes. Please also observe the further product documentation!

WAGO Kontakttechnik GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

Material Data

Color	white
Material	PET
Halogen-free	Yes
Weight	220 g

Environmental Requirements

Surrounding air (storage) temperature	10 ... 22 °C
Surrounding air (operating) temperature	-20 ... 80 °C
Relative humidity	40 ... 50 %







Commercial data

Product Group	2 (Terminal Block Accessories)
Packaging type	BOX
Country of origin	DE
GTIN	4050821675006
Customs Tariff No.	39269097900





Counterpart

Compatible products

Marking accessories

	Item no.: 211-823 Nozzles; Length: 23 mm; For the use of 211-821; halogen-free; Cable outer diameter: 1.4 ... 5.0 mm	www.wago.com/211-823
	Item no.: 211-824 Nozzles; Length: 23 mm; For the use of 211-821; halogen-free; Cable outer diameter: 5.0 ... 11.0 mm	www.wago.com/211-824
	Item no.: 211-829 Nozzles; Length: 23 mm; For the use of 211-821; halogen-free	www.wago.com/211-829
	Item no.: 211-922 Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 1.5 ... 2.5 mm	www.wago.com/211-922
	Item no.: 211-923 Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 2.0 ... 4.0 mm	www.wago.com/211-923
	Item no.: 211-924 Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 4.0 ... 7.0 mm	www.wago.com/211-924
	Item no.: 211-925	

Subject to changes. Please also observe the further product documentation!

	Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 6.0 ... 10.0 mm	www.wago.com/211-925
	Item no.: 211-926 Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 10.0 ... 14.0 mm; transparent	www.wago.com/211-926
	Item no.: 211-927 Nozzles; Length: 23 mm; For the use of 211-821; halogenated; Cable outer diameter: 14.0 ... 22.0 mm; transparent	www.wago.com/211-927
	Item no.: 258-5000 Thermal transfer printer; Smart Printer; for complete control cabinet marking; 300 dpi	www.wago.com/258-5000

Downloads

Documentation

Additional Information

211-821, Information on handling print material	V002.08.2017	pdf 1.6 MB	Download
---	--------------	---------------	----------

Installation Notes

Marking



Remove the printed marker from the reel.




Slide the marker into the marking sleeve receptacle. Exchanging the marker is also possible after the conductor has been terminated.



Slide the marker through the marker slot up to the end of the sleeve.

Subject to changes. Please also observe the further product documentation!



Then remove the rest of the card by twisting it off.

Subject to changes. Please also observe the further product documentation!